

The Philips logo is displayed in a white rounded rectangle on a teal background.

Headlight Restoration Kit



Headlight Restoration Kit

with UV Protection

See clearly. Drive safer.

Yellow, hazy headlight lenses are an eyesore and a danger to your customers and their passengers. Philips Headlight Restoration Kit takes the haze away, restoring the headlights to like-new condition and finish. Plus, our unique UV protection formula provides two years of protection from re-hazing.

Compared with other kits that require power tools, our advanced

technology delivers excellent results with minimal effort and is extremely simple to use. In four easy steps, consumers can achieve professional results with no power tools needed.

Philips offers high quality products for more safety, and the Philips Headlight Restoration Kit is the solution for making the most of your driving experience.

Can Be Used on:

Headlights | Taillights

Turn Signal Lights & Reflective Lens Covers

Please contact your Lumileds sales account manager or customer service at:

866-254-6989

philipsautoorders@lumileds.com



Philips Headlight Restoration Kit

Order Kit:
HRKOOXM

Professional results in under 30 minutes:



- Restores headlight lenses to like-new condition
- UV coating technology: restore rather than replace
- Up to 100% brighter with less glare
- Provides safer nighttime driving
- High quality and cost-effective
- No power tools needed
- Cleans both headlights
- Removes haze and yellowing from sun and dirt
- 2 years UV protection

Contents & Directions:

Headlight Restoration Kit Contents	
Description	Qty.
1oz. – Water based pretreatment	1
1oz. – Cleaner/Polish	1
1oz. – Shine Restorer/Preserver	1
2-3/4" x 3" 600 Grit sandpaper (coarse)	1
2-3/4" x 3" 1500 Grit sandpaper (medium)	1
2-3/4" x 3" 2000 Grit sandpaper (fine)	1
Paper towels	10
Gloves	2

Step 1: Clean with water-based pretreatment.

Step 2: Sand with 600, 1500 and 2000 grit sandpaper.*

Step 3: Polish with headlight/cleaner polish

Step 4: Apply UV restorer/protector. Dries in 10min.

**Skip step 600 grit sandpaper if lens has no extensive grazing and pits.*

Scan QR code, or go to:
<https://goo.gl/N5gpfA>
to watch the
instructional video.



Lumileds
34119 W. Twelve Mile Road, Suite 102
Farmington Hills, MI 48331
Phone: 800-257-6054
www.philips.com/automotive

